

# PHILIPS

Candle & Lustre

LED

5.5W-40W

E14

Warm White



8718696828175



## Bright LED lighting

Philips LED light bulbs provide high-quality light, an exceptionally long life and immediate, significant energy savings.

### High-quality light

- Learn about light

### Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

# Highlights

## Learn about light



Colour temperature: light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energising light. CRI: the colour rendering index (CRI) is used to describe the effect of a light source on colour appearance. Natural sunlight

has a CRI of 100. The CRI of Philips LED lamps is always higher than 80, which ensures that colours are shown as true and natural.

## Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Technology: LED
- Type of glass: Frosted

## Lamp dimensions

- Height: 10.8 cm
- Weight: 0.024 kg
- Width: 3.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 15,000

## Light characteristics

- Beam angle: 200 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Light Colour Category: Warm White
- Nominal luminous flux: 470 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

## Other characteristics

- Lamp current: 45 mA
- Efficacy: 85 lm/W

## Packaging information

- EAN: 8718696828175
- EOC: 871869682817500
- Product title: LED 40W B35 E14 WW FR ND 3CT/6 DISC

## Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 5.5 W
- Wattage equivalent: 40 W

## Product dimensions and weight

- Length: 10.8 cm

## Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 470 lm
- Rated power: 5.5 W

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718696828175
- Net weight: 90.000 g
- Gross weight: 111.200 g
- Height: 10.900 cm
- Length: 3.800 cm
- Width: 11.300 cm
- Material number (12NC): 929001253694



Issue date: 2023-11-08  
Version: 0.260

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)