PHILIPS

Bulb

LED

8W-70W

Cool Daylight

8718696844014



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities with Wider Light Spread. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light
- Designed for the comfort of your eyes
- Light all around

Choose for a sustainable solution
- Safe for any room and convenient to recycle
- You can trust what the Philips packaging is saying.

Create the right light for your home
- Light you can direct

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Light you can direct

The adjustable swivel head allows you to direct the light exactly where you like it and provides a wider light spread, making it the perfect replacement for any bulb.

Specifications

Characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: T-shape
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions
- Height: 20 cm
- Weight: 0.1 kg
- Width: 3 cm

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 7,500

Light characteristics
- Color rendering index (CRI): 70
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous
- EyeComfort: Yes

Other characteristics
- Lamp current: 60 mA
- Efficacy: 100 lm/W

Packaging information
- Product family: LED
- EAN: 8718696844014
- EOC: 871869684401400
- Product title: T-Bulb CW 8W B22

Power consumption
- Power factor: 0.9
- Voltage: 220-240 V
- Wattage: 8 W
- Wattage equivalent: 70 W
- Energy Efficiency Label (EEL): 3 star

Product dimensions & weight
- Length: 9.7 cm

Rated values
- Rated luminous flux: 800 lumen
- Rated power: 8 W

Technical specifications
- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718696844014
- Net weight: 98.000 g
- Gross weight: 130.000 g
- Height: 11.000 cm
- Length: 20.000 cm
- Width: 3.000 cm
- Material number (12NC): 929001923213

Issue date: 2023-11-08
Version: 0.253

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com