

PHILIPS

Bulb

LED

5.5W-55W

E27 cap

White

8718696844755



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker
- Light all around

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11.43 cm
- Weight: 0.038 kg
- Width: 3.72 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 550 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 70 mA
- Efficacy: 100 lm/W

Packaging information

- EAN: 8718696844755
- EOC: 871869684475500
- Product title: DLStick 5.5W E27 3000K 1PF/12 APR

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 5.5 W
- Wattage equivalent: 55 W

Product dimensions & weight

- Length: 11.43 cm

Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 550 lumen
- Rated power: 5.5 W

Technical specifications

- Frequency: 50–60 Hz

Bulb characteristics

- EAN/UPC - product: 8718696844755
- Rated beam angle: 200 degree(s)
- Height: 11.43 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 200 degree(s)
- Lamp current: 70 mA
- Net weight: 0.030 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.038 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.043 kg
- EAN: 8718696844755
- Rated luminous flux: 550 lumen
- Lamp shape: Non directional bulb
- Width: 3.72 cm
- Color rendering index (CRI): 80
- Height: 14.700 cm
- EOC: 871869684475500
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 3000 K
- EyeComfort: Yes
- Length: 3.900 cm
- Product title: DLStick 5.5W E27
3000K 1PF/12 APR
- Power factor: 0.51
- Rated power: 5.5 W
- Technology: LED
- Light Color Category: White
- Width: 3.900 cm
- Voltage: 220-240 V
- Type of glass: Frosted
- Nominal luminous flux: 550 lumen
- Material number (12NC):
929001900907
- Wattage: 5.5 W
- Length: 11.43 cm
- Starting time: <0.5 s
- Wattage equivalent: 55 W
- Warm-up time to 60% light: Instant
full light
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.134

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com