

# PHILIPS

Bulb

LED

15W-100(100W GLS, 20W CFL)W

B22

Cool daylight

8718699619022



## State-of-the-art LED for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Learn about light

### Light beyond illumination

- A simple LED for everyday use
- Instant on

# Highlights

## Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more

tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. CRI: the color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED light bulbs is always higher than 80, which ensures colors are shown as true and natural.

## Instant on

## A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 8.2 cm
- Weight: 0.125 kg
- Width: 15 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1300 lumen
- Starting time: 0.45 s
- Warm-up time to 60% light: Instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 125 mA
- Efficacy: 86 lm/W

#### Packaging information

- EAN: 8718699619022
- EOC: 871869961902200
- Product title: UFO LEDBulb 15W B22 6500K 230V 1CT/6

#### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 15 W
- Wattage equivalent: 100(100W GLS, 20W CFL) W

#### Product dimensions & weight

- Length: 8.2 cm

#### Rated values

- Rated beam angle: 120 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1300 lumen
- Rated power: 15 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions & weight

- EAN/UPC - product: 8718699619022
- Net weight: 0.137 kg
- Gross weight: 0.154 kg
- Height: 15.500 cm
- Length: 15.500 cm
- Width: 8.500 cm
- Material number (12NC): 929001971707



Issue date: 2021-05-05  
Version: 0.224

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)