

PHILIPS
LED
Bulb
24W-100(150W GLS,
40W CFL)W
E27
White

8718699619046



State-of-the-art LED for the home

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Learn about light

Light beyond illumination

- A simple LED for everyday use
- Instant on

PHILIPS

Highlights

Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more

tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. CRI: the color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED light bulbs is always higher than 80, which ensures colors are shown as true and natural.

Instant on

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 8.2 cm
- Weight: 0.235 kg
- Width: 20 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 2150 lumen
- Starting time: 0.45 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 210 mA
- Mercury content: 0 mg
- Efficacy: 89 lm/W

Packaging information

- EAN: 8718699619046
- EOC: 871869961904600
- Product title: UFO LEDBulb 24W E27 3000K 230V 1CT/6

Power consumption

- Power consumption per 1000h: 24 kW
- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 24 W
- Wattage equivalent: 100(150W GLS, 40W CFL) W

Rated values

- Rated beam angle: 120 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 2150 lumen
- Rated power: 24 W

Packaging dimensions & weight

- SAP EAN/UPC - Piece: 8718699619046
- EAN/UPC - Case: 8718699619053
- SAP Gross Weight EAN (Piece): 0.240 kg
- Net Weight: 0.220 kg
- SAP Height (Piece): 21.000 cm
- SAP Length (Piece): 21.000 cm
- SAP Width (Piece): 8.500 cm



Issue date: 2019-11-28
Version: 0.148

© 2019 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com