



PHILIPS
LED
Bulb
19W-155W
B22
Warm White

8718699640590

State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- No visible flicker

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Designed to be seen, looks good on and off

- Looks good on and off

PHILIPS

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate

the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED

Bulb dimensions

- Height: 15.5 cm
- Weight: 0.15 kg
- Width: 8 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 2150 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: No

Other characteristics

- Lamp current: 170 mA
- Mercury content: 0 mg
- Efficacy: 113 lm/W

Packaging information

- EAN: 8718699640590
- EOC: 871869964059000
- Product title: LEDBulb 19W B22 3000K 230VA80 1CT/6APR

Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 19 W
- Wattage equivalent: 155(155W for Incandescent;35W CFL) W

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 10,000 hour(s)
- Rated luminous flux: 2150 lumen
- Rated peak intensity: N/A cd
- Rated power: 19 W

Packaging dimensions and weight

- EAN/UPC - product: 8718699640590
- Net weight: 0.147 kg
- Gross weight: 0.187 kg
- Height: 16.200 cm
- Length: 8.200 cm
- Width: 8.200 cm
- SAP EAN/UPC - Piece: 8718699640590
- Material number (12NC): 929002004649
- EAN/UPC - Case: 8718699640606
- SAP Gross Weight EAN (Piece): 0.187 kg
- Net Weight: 0.147 kg
- SAP Height (Piece): 16.200 cm
- SAP Length (Piece): 8.200 cm
- SAP Width (Piece): 8.200 cm



Issue date: 2020-05-16
Version: 0.67

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com