



PHILIPS
LED
Bulb
14W-84W
B22
Cool daylight

8718699654115

A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- A simple LED for everyday use

PHILIPS

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11.9 cm
- Weight: 0.069 kg
- Width: 6.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 15,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1521 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 110 mA
- Mercury content: 0 mg
- Efficacy: 108 lm/W

Packaging information

- EAN: 8718699654115
- EOC: 871869965411500
- Product title: LEDBulb 14W B22 6500K 230V 1CT/6 AU

Power consumption

- Power consumption per 1000h: 14 kW
- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 14 W
- Wattage equivalent: 84 W
- Energy Efficiency Label: A+

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1521 lumen
- Rated power: 14 W

Packaging dimensions & weight

- EAN/UPC - product: 8718699654115
- Net weight: 0.120 kg
- Gross weight: 0.142 kg
- Height: 11.700 cm
- Length: 6.700 cm
- Width: 6.700 cm
- EAN/UPC - Piece: 8718699654115
- Material number (12NC): 929002043749
- EAN/UPC - Case: 8718699654122
- Weight product including package: 0.142 kg
- Weight product without package: 0.120 kg
- SAP Height (Piece): 11.700 cm
- SAP Length (Piece): 6.700 cm
- SAP Width (Piece): 6.700 cm



Issue date: 2020-03-30
Version: 0.13

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com