PHILIPS

Bulb (Dimmable)

LED

11W-75W

B22

Warm Glow

Dimming

8718699654955



Experience dimmable, warm white LED light

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Light beyond illumination

- Dimmable
- Instant on

Highlights

Dimmable
This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

Instant on

Specifications

Characteristics
- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions
- Height: 11 cm
- Weight: 0.075 kg
- Width: 6 cm

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics
- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2200-2700 K
- Light Color Category: Warm Glow
- Nominal luminous flux: 1055 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics
- Lamp current: 65 mA
- Efficacy: 95 lm/W

Packaging information
- EAN: 8718699654955
- EOC: 871869965495500
- Product title: LEDBulb 11-75W A60 B22 2700K FR D AU/BC

Power consumption
- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 11 W
- Wattage equivalent: 75(75W GLS, 17W CFL) W
- Energy Efficiency Label (EEL): A+

Product dimensions & weight
- Length: 11 cm

Rated values
- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 1055 lumen
- Rated power: 11 W

Technical specifications
- Frequency: 50-60 Hz

Packaging dimensions & weight
- EAN/UPC - product: 8718699654955
- Net weight: 0.050 kg
- Gross weight: 0.075 kg
- Height: 15.300 cm
- Length: 6.500 cm
- Width: 7.200 cm
- Material number (12NC): 929001353279

Issue date: 2023-11-07
Version: 0.71

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com