

PHILIPS

Spot

LED

3.2W-50W

GU10

Cool Daylight

8718699659325



Durable LED accent lighting with a focused bright beam

Philips LED spots provide a focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

Choose for a sustainable solution

- Safe for any room and convenient to recycle

Create the right light for your home

- Perfect for accent lighting

Highlights

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

Perfect for accent lighting



Modern lighting with a familiar wide angle light output (36 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

Bulb dimensions

- Height: 5.4 cm
- Weight: 0.036 kg
- Width: 5 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 320 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: No

Other characteristics

- Lamp current: 30 mA
- Efficacy: 115 lm/W

Packaging information

- EAN: 8718699659325
- EOC: 871869965932500
- Product title: Essential LED 3.2-50W GU10 865 36D1PF/10

Power consumption

- Power factor: 0.4
- Voltage: 220-230 V
- Wattage: 3.2 W
- Wattage equivalent: 50 W
- Energy Efficiency Label (EEL): A++

Product dimensions & weight

- Length: 5.4 cm

Rated values

- Rated beam angle: 36 degree(s)
- Rated lifetime: 10,000 hour(s)
- Rated luminous flux: 320 lumen
- Rated peak intensity: 600 cd
- Rated power: 3.2 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699659325
- Net weight: 0.032 kg
- Gross weight: 0.047 kg
- Height: 8.900 cm
- Length: 5.100 cm
- Width: 5.100 cm
- Material number (12NC): 929002057507



Issue date: 2021-03-02
Version: 0.13

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com