PHILIPS

Bulb

LED

9W-50(50W halogen,15W CFL)W

B22

Warm White

8718699670016



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light
- No visible flicker

Choose for a sustainable solution
- You can trust what the Philips packaging is saying.

Create the right light for your home
- A simple LED for everyday use

Highlights

No visible flicker
When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR
The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A Simple LED for Everyday Use
The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions
- Height: 10.5 cm
- Weight: 0.03 kg
- Width: 6 cm

Durability
- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics
- Beam angle: 180 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 806 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous
- EyeComfort: No

Other characteristics
- Lamp current: 70 mA
- Efficacy: 89 lm/W

Packaging information
- EAN: 8718699670016
- EOC: 871869967001600
- Product title: LEDBulb 9W B22 2700K 230V 2CT/3 AU

Power consumption
- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 9 W
- Wattage equivalent: 50 W

Product dimensions & weight
- Length: 10.5 cm

Rated values
- Rated beam angle: 180 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 806 lumen
- Rated power: 9 W

Technical specifications
- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699670016
- Net weight: 0.084 kg
- Gross weight: 0.109 kg
- Height: 10.700 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC): 929002310279

Issue date: 2023-11-08
Version: 0.140

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com