

# PHILIPS

Recessed spot light

Functional

DL252

White



8718699670313



## Comfortable light with a slimmer fit

Philips LED Slim Downlight provides a slim and non-intrusive fitting ideal for rooms with low false ceilings

### Match your interior

- Super slim design

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Light effect

- Bright light with uniform distribution
- Side emitting LED with anti glare to ease your eyes

### Safety

- No harmful UV radiation

### Material & finishing

- High quality metal material

### Durability

- Long life span up to 15,000 hours

# Highlights

## Super slim design

Slim design is ideal for low-ceiling rooms, sitting flush against the surface.

## Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## Side emitting LED with anti glare to ease your eyes

Comfortable for your eyes, the side-emitting LED distributes light evenly without distracting you.

## No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

## High quality metal material

Durable and attractive metal material for a strong finish.

## Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

# Specifications

## Design and finishing

- Color: white
- Material: metal/plastic

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

## Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

## Miscellaneous

- Especially designed for: Functional
- Type: Downlight

## Product dimensions & weight

- Cut out length: 7.3 cm
- Cut out width: 7.3 cm
- Height: 2 cm
- Length: 8.5 cm
- Net weight: 0.091 kg
- Recessed distance: 5 cm
- Width: 8.5 cm

## Service

- Warranty: 1 year(s)

## Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 85 mm
- Total lumen output fixture: 210
- Light color: 3000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 4
- IP code: IP20
- Class of protection: Class II

## Packaging dimensions and weight

- EAN/UPC - product: 8718699670313
- Net weight: 0.091 kg
- Gross weight: 0.121 kg
- Height: 9.500 cm
- Length: 9.500 cm
- Width: 4.700 cm
- Material number (12NC): 929002098801



Issue date: 2023-11-08  
Version: 0.155

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)