

PHILIPS

Ceiling light

Functional


CL505

White

RF Dimming



8718699680954



Set your desired ambience at your fingertips

Create the right ambience every time. With just a couple of clicks on the remote control, Philips LED all-in-one ceiling light gives you the flexibility and convenience to choose between a range of light settings for every moment.

Light effect

- SceneSwitch color change
- Uniform light distribution

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Dimmable
- 4 pre-set scenes

Durability

- Long life span up to 15,000 hours

Highlights

SceneSwitch color change

SceneSwitch Color Change lets you set the overall mood of a living space at home. Stay focused with cool daylight, be more productive with cool white light or wind down and relax with warm white light. In essence, consumers can control the lights in their home according to their daily activities.

Uniform light distribution

Throw light across your rooms in an even and uniform manner.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a

decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom
- Type: Ceiling light

Product dimensions and weight

- Net weight: 0.7 kg
- Height: 8.5 cm
- Length: 36.8 cm
- Width: 36.8 cm

Service

- Warranty: 5 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 368 mm
- Total lumen output fixture: 2800
- Light color: 2700-6500
- Mains power: 220-240
- Fixture dimmable: RF Dim – Do not use with dimmer
- LED: Yes
- Built in LED: Yes
- Fixture is compatible with bulb(s) of class: A+
- Wattage bulb included: 23
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC – product: 8718699680954
- Net weight: 0.7 kg
- Gross weight: 1.12 kg
- Height: 8.5 cm
- Length: 41.5 cm
- Width: 41.5 cm
- Material number (12NC): 915005772801



Issue date: 2023-11-08
Version: 0.515

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com