

PHILIPS

Bulb

LED

9W-55(55W halogen,15W
CFL)W

B22

Warm White

8718699688288



State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- No visible flicker
- Cool, energizing light

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 10.4 cm
- Weight: 0.05 kg
- Width: 5.8 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 130 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 900 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: No

Other characteristics

- Lamp current: 80 mA
- Efficacy: 100 lm/W

Packaging information

- EAN: 8718699688288
- EOC: 871869968828800
- Product title: ESS LEDBulb 9W B22 3000K 230V 3CT/4 AU

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 9 W
- Wattage equivalent: 55 W

Product dimensions & weight

- Length: 10.4 cm

Rated values

- Rated beam angle: 130 degree(s)
- Rated lifetime: 10,000 h
- Rated luminous flux: 900 lumen
- Rated peak intensity: 150 cd
- Rated power: 9 W

Technical specifications

- Frequency: 50-60 Hz

**Packaging dimensions & weight [ESS
LEDBulb 9W B22 3000K 230V 3CT/4
AU]**

- EAN/UPC - product: 8718699688288
- Net weight: 0.170 kg
- Gross weight: 0.209 kg
- Height: 11.500 cm
- Length: 6.100 cm
- Width: 14.900 cm
- Material number (12NC):
929002308269

**Packaging dimensions & weight [ESS
LEDBulb 9W B22 3000K 230V 3CT/4
AU]**

- EAN/UPC - product: 8718699688288
- Net weight: 0.174 kg
- Gross weight: 0.203 kg
- Height: 9.900 cm
- Length: 5.800 cm
- Width: 16.400 cm
- Material number (12NC):
929001899969



Issue date: 2021-09-22
Version: 0.152

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.