

# PHILIPS

Bulb

LED

9W-58(58W halogen,15W  
CFL )W

B22

Cool Daylight

8718699688462



## State-of-the-art LED light bulb for the home

Philips LED light bulbs provide a beautiful, warm white light, a long lifetime, and immediate, significant energy savings. With its modern and elegant design, this dimmable bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- No visible flicker
- Cool, day light

### Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## Cool, day light



This bulb has a color temperature of 6500K, and is the highest color temperature available in this bulb category. It therefore gives you a

lighting effect that is the closest to that of natural daylight. This will help you focus and experience every detail.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22

## Bulb dimensions

- Height: 10.4 cm
- Width: 5.8 cm

## Durability

- Nominal lifetime: 10,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 130 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 950 lm
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Efficacy: 105 lm/W

## Packaging information

- EAN: 8718699688462
- EOC: 871869968846200
- Product title: ESS LEDBulb 9W B22 6500K 230V 4CT/3 AU

## Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 9 W
- Wattage equivalent: 58 W

## Product dimensions and weight

- Length: 10.4 cm

## Rated values

- Rated peak intensity: 150 cd

## Technical specifications

- Frequency: 50-60 Hz

## Packaging dimensions & weight

- EAN/UPC - product: 8718699688462
- Net weight: 0.2 kg
- Gross weight: 0.26 kg
- Height: 11.8 cm
- Length: 6.1 cm
- Width: 24.8 cm
- Material number (12NC): 929002308479



Issue date: 2024-02-02  
Version: 0.159

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)