

# PHILIPS

## Ceiling light

Functional


UltraGlow ceiling light

Warm White

22W, Round



8718699690144



## High quality LED Ceiling light designed to last for years

Philips LED ceiling lights provide light that is designed for the comfort of your eyes.

### Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

### Light effect

- Bright light with uniform distribution

### Premium quality

- EyeComfort - light that's easy on the eyes

### Durability

- Long life span up to 25,000 hours

# Highlights

## **Suitable for low ceilings Slim design Bright light with uniform distribution**

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

## **Eyecomfort**

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

## **Long life span up to 25,000 hours**

Philips LED technology extends your product's lifetime up to 25,000 hours

# Specifications

## **Bulb characteristics**

- Intended use: Indoor
- Lamp shape: Round

## **Design and finishing**

- Color: White
- Material: plastic

## **Durability**

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Number of switch cycles: 10,000

## **Extra feature/accessory incl.**

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

## **Light characteristics**

- Beam angle: 120 degree(s)
- Color consistency: 5
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## **Miscellaneous**

- Especially designed for: Functional

## **Other characteristics**

- Lamp current: 80 mA
- Efficacy: 75 lm/W

## **Power consumption**

- Power factor: 0.9
- Voltage: 220-240 V

**Product dimensions and weight**

- Net weight: 0.265 kg
- Cut out length: 18.8 cm
- Cut out width: 18.8 cm
- Height: 2.2 cm
- Length: 22.5 cm
- Width: 22.5 cm

**Service**

- Warranty: 2 year(s)

**Technical specifications**

- Lifetime up to: 25,000 hour(s)
- Diameter: 225 mm
- Total lumen output fixture: 1650
- Light color: 3000
- Mains power: 220–240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 22
- IP code: IP20
- Class of protection: Class II

**Packaging dimensions and weight  
[22W Round AP Plus UltraGlow LED  
DL(WW)]**

- EAN/UPC – product: 8718696584958
- Net weight: 0.280 kg
- Gross weight: 0.390 kg
- Height: 23.500 cm
- Length: 25.000 cm
- Width: 4.000 cm
- Material number (12NC):  
929002629501

**Packaging dimensions and weight  
[22W Round AP LED Plus (WW)]**

- EAN/UPC – product: 8718696584958
- Net weight: 0.280 kg
- Gross weight: 0.390 kg
- Height: 23.500 cm
- Length: 25.000 cm
- Width: 4.000 cm
- Material number (12NC):  
929001951776



Issue date: 2023-11-08  
Version: 0.176

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)