

PHILIPS

Bulb

LED

14W-84W

B22

2700-6500

8718699700478



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- No visible flicker

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- A simple LED for everyday use

Highlights

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Accessory
- Socket: B22
- Technology: LED

Durability

- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700–6500 K
- Light Color Category: Cool Daylight / Warm White
- Nominal luminous flux: 1521 lumen
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 40 mA
- Efficacy: 108 lm/W

Packaging information

- EAN: 8718699700478
- EOC: 871869970047800
- Product title: LEDBulb 14W B22 WW/CDL 230V 2CT/12 AU

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 14 W
- Wattage equivalent: 84 W

Product dimensions & weight

- Length: 4.8 cm

Rated values

- Rated luminous flux: 1521 lumen
- Rated power: 14 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8718699700478
- Net weight: 0.120 kg
- Gross weight: 0.140 kg
- Height: 11.800 cm
- Length: 6.600 cm
- Width: 11.500 cm
- Material number (12NC): 929002266919



Issue date: 2021-03-02
Version: 0.14

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com