

# PHILIPS

Bulb

LED

4W-40(GLS 40, CLFi 7)W

E14

White

8718699701635



## Beautify your home with Philips LED globe bulbs

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- No visible flicker
- Cool, energizing light

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambiance for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 8.8 cm
- Weight: 0.02 kg
- Width: 4.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 350 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 930 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 35 mA
- Efficacy: 87 lm/W

## Packaging dimensions and weight

- Net weight: 0.021 kg

## Packaging information

- EAN: 8718699701635
- EOC: 871869970163500
- Product title: LEDBulb 4W E14 3000K 230V P45 9 APR

#### Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 4 W
- Wattage equivalent: 40 W

#### Product dimensions & weight

- Length: 8.8 cm

#### Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 350 lumen
- Rated power: 4 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions and weight [LEDBulb 4W E14 3000K 220V P45(APR)]

- EAN/UPC – product: 8718699701635
- Gross weight: 0.042 g
- Height: 8.600
- Length: 4.600
- Width: 4.600
- Material number (12NC):  
929002267507

#### Packaging dimensions and weight [LEDBulb 4W E14 3000K 230V P45 9 APR]

- EAN/UPC – product: 8718699701635
- Gross weight: 0.029 g
- Height: 8.750
- Length: 4.650
- Width: 4.650
- Material number (12NC):  
929002975007



Issue date: 2023-11-08  
Version: 0.33

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)