

# PHILIPS

Bulb

LED

6.5W-45(GLS 45, CLFi 10)W

E14

Cool Daylight

8718699701697



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- Instant on

### High quality LED light that lasts for decades

- Light that shows true colors

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Instant on Light that shows true colors



See the true colors of your clothes when you select an outfit from your wardrobe – you can pair a red dress and red shoes with confidence and be sure the colors match perfectly.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 9.6 cm
- Weight: 0.034 kg
- Width: 5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 550 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 55 mA
- Efficacy: 84 lm/W

## Packaging information

- EAN: 8718699701697
- EOC: 871869970169700
- Product title: LEDBulb 6.5W E14 6500K 220V P50(APR)

#### Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 6.5 W
- Wattage equivalent: 45 W

#### Product dimensions & weight

- Length: 9.6 cm

#### Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 550 lumen
- Rated power: 6.5 W

#### Technical specifications

- Frequency: 50–60 Hz

#### Packaging dimensions and weight

##### [LEDBulb 6.5W E14 6500K 230V P48 9 APR]

- EAN/UPC – product: 8718699701697
- Net weight: 0.023 kg
- Gross weight: 0.036 g
- Height: 9.900
- Length: 5.100
- Width: 5.100
- Material number (12NC): 929002975507

#### Packaging dimensions and weight

##### [LEDBulb 6.5W E14 6500K 220V P50(APR)]

- EAN/UPC – product: 8718699701697
- Net weight: 0.034 kg
- Gross weight: 0.047 g
- Height: 9.900
- Length: 5.100
- Width: 5.100
- Material number (12NC): 929002267407



Issue date: 2023-11-08  
Version: 0.177

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)