

PHILIPS

Bulb

LED

4W-35W

E27

Cool Daylight

8718699704544



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Create the right light for your home

- A simple LED for everyday use

Light beyond illumination

- Instant on

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Instant on Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off. "

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 8.8 cm
- Weight: 0.025 kg
- Width: 4.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 330 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 30 mA
- Efficacy: 82 lm/W

Packaging information

- EAN: 8718699704544
- EOC: 871869970454400
- Product title: LEDBulb 4W E27 6500K 230V P45 AU

Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 35 W

Product dimensions & weight

- Length: 8.8 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 330 lumen
- Rated power: 4 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699704544
- Net weight: 0.026 kg
- Gross weight: 0.036 kg
- Height: 11.600 cm
- Length: 4.600 cm
- Width: 4.600 cm
- Material number (12NC): 929002039769



Issue date: 2021-05-05
Version: 0.136

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com