

PHILIPS

Bulb

LED

20W-125W

B22

White

8718699717018



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High quality light

- Cool, day light

Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Safe for any room and convenient to recycle
- You can trust what the Philips packaging is saying.

Light beyond illumination

- Instant on

Highlights

Cool, day light



This bulb has a color temperature of 6500K, and is the highest color temperature available in this bulb category. It therefore gives you a lighting effect that is the closest to that of natural daylight. This will help you focus and experience every detail.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Instant on

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 13 cm
- Weight: 0.106 kg
- Width: 6.8 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 7,500

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 1800 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 90 mA
- Efficacy: 90 lm/W

Packaging information

- Product family: LED
- EAN: 8718699717018
- EOC: 871869971701800
- Product title: Stellar Bright WW 20W B22

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V
- Wattage: 20 W
- Wattage equivalent: 125 W
- Energy Efficiency Label (EEL): 3 star

Product dimensions & weight

- Length: 10.7 cm

Rated values

- Rated luminous flux: 1800 lumen
- Rated power: 20 W

Technical specifications

- Frequency: 50

Packaging dimensions and weight

- EAN/UPC - product: 8718699717018
- Net weight: 0.103 kg
- Gross weight: 0.134 kg
- Height: 13.750 cm
- Length: 6.900 cm
- Width: 6.800 cm
- Material number (12NC):
929002268713



Issue date: 2020-09-21
Version: 0.131

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com