

# PHILIPS

Bulb

LED

40W-45W

B22

White

8718699718497



## Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High quality light

- Designed for the comfort of your eyes
- Light all around

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years
- Safe for any room and convenient to recycle
- You can trust what the Philips packaging is saying.

### Light beyond illumination

- Instant on

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## No hazardous substances

Philips LED lights contain absolutely no hazardous materials, making them safe for any room and convenient to recycle.

## No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

## Instant on

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: B22
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 22 cm
- Weight: 0.297 kg
- Width: 12 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 7,500

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 3600 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 170 mA
- Efficacy: 90 lm/W

## Packaging information

- Product family: LED
- EAN: 8718699718497
- EOC: 871869971849700
- Product title: StellarBright Bulb 40W 3600lm B22d 3000K

#### Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage: 40 W

#### Product dimensions and weight

- Length: 10.7 cm

#### Rated values

- Rated luminous flux: 3600 lumen
- Rated power: 40 W

#### Technical specifications

- Frequency: 50 Hz

#### Packaging dimensions and weight

- EAN/UPC – product: 8718699718497
- Net weight: 0.210 kg
- Gross weight: 0.280 kg
- Height: 20.000 cm
- Length: 10.100 cm
- Width: 10.100 cm
- Material number (12NC):  
929002295113



Issue date: 2023-11-08  
Version: 0.159

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)