

PHILIPS

Starter kit: 2 B22
smart bulbs (800)

Hue White

Up to 800 lumens*

Soft white light

Smart control

Hue Bridge included

8718699718893



Easy smart lighting

Enhance your lighting experience with a Philips Hue White B22 starter kit. Connect your warm white bulbs to the included Hue Bridge to take advantage of features such as wireless dimming, routines and timers.

Limitless possibilities

- Away-from-home smart light control
- Come home to a house filled with light
- Make it look like you're home with smart lights
- Control lights with your voice

Highlights

Control lights away from home




The Philips Hue app gives you complete control over your lights, even if you're not home. Switch your lights off and on remotely using just the app to ensure your home is always lit the way you want it.

Make it look like you're home



Use the Philips Hue app to schedule light routines whenever you're away. Your smart lights will turn on at the times you've selected • and sometimes a few minutes before or after • to truly mimic your presence in the house.

Control with your voice



When connected to the Hue Bridge, you can pair your lights with Alexa, Apple HomeKit, and the Google Assistant and control your lights using just your voice. Simple voice commands let you turn your lights on and off, dim or brighten your lights, and even set a light scene.

Come home with light



Set your Philips Hue app to recognize when you're nearing home. Before you even step out of your car or walk up the path, your selected smart lights turn on automatically.

Specifications

Bulb dimensions

- Dimensions (WxHxD): 62x110

Design and finishing

- Color: white

Environmental

- Operational humidity: 5% <H<95% (non condensing)
- Operational temperature: -20°C to 45°C

Extra feature/accessory incl.

- Dimmable with Hue app and switch: Yes

Guarantee

- 2 years: Yes

Light characteristics

- Color rendering index (CRI): 80

Packaging information

- EAN: 8718699718893

Service

- Warranty: 2 year(s)

Technical specifications

- Weight: 78
- Bulb technology: LED
- Lumen output at 2700K: 806 lumen

The bridge

- Diameter: 88 mm
- Frequency band: 2400–2483,5 MHz
- Height: 26 mm
- Max. number of accessories: 12
- Max. number of bulbs: 50
- Mounting options: Desktop, Wall
- Power adapter: 100–240 V AC / 50–60Hz
- Power consumption: 250mA max

The bulb

- Brightness: 800
- Color temperature: 2700K
- Diameter: 61 mm
- Fitting: B22
- Form factor: A60
- Height: 110 mm
- Input voltage: 220V–240V
- Lifetime: 25,000 h
- Light output: Soft white light
- Lumen output: 806 lm
- Max. operation power: 9 W
- Max. standby power: 0.5 W
- Number of switching cycles: 50,000
- Power factor: >0.5
- Rated lifetime: 25,000 h
- Software upgradable: Yes
- Start up: Instant 100% light output
- Wattage: 9 W
- Wattage equivalent: 60 W
- Communication protocol: Bluetooth and Zigbee
- Deep dimmable: Yes
- Software upgradable: When connected to Bluetooth App or Hue Bridge

The switch

- IP rating: IP 20

What's in the box

- Bridge: 1
- Ethernet network cable: 1
- Hue bulbs: 2
- Power adapter: 1

What's supported

- HomeKit compatible: YES
- Philips Hue App: IOS 14 and above, Android 10.0 and above
- Voice assistants: Amazon Alexa, Apple HomeKit (Via Hue Bridge), Google Assistant, Microsoft Cortana (Via Hue Bridge)

Packaging dimensions & weight

- EAN/UPC – product: 8718699718893
- Net weight: 0.446 kg
- Gross weight: 0.566 kg
- Height: 21.000 cm
- Length: 8.200 cm
- Width: 21.000 cm
- Material number (12NC): 929001821710



Issue date: 2023-11-07
Version: 0.510

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com