

PHILIPS

Candle & Lustre

LED

5W-50W

B15

Warm White

8718699723088



Bright LED lighting

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Learn about light
- Light all around

Choose a simple replacement for your old bulbs

- Similar shape and size as halogen luster

Light beyond illumination

- Instant on

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. CRI: the color rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED

light bulbs is always higher than 80, which ensures colors are shown as true and natural.

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

Replaces luster halogen



With its beautifully shaped design and familiar dimensions, this is a modern lighting, LED luster. The perfect sustainable replacement for traditional halogen lusters.

Instant on

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: B15
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 8.6 cm
- Weight: 0.03 kg
- Width: 4.5 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 h
- Number of switch cycles: 30,000

Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 470 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 50 mA
- Efficacy: 94 lm/W

Packaging information

- EAN: 8718699723088
- EOC: 871869972308800
- Product title: LEDLuster 5-50W B15 827 P45NDFR AU 2CT

Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 5 W
- Wattage equivalent: 50 W

Product dimensions & weight

- Length: 8.6 cm

Rated values

- Rated lifetime: 10,000 h
- Rated luminous flux: 470 lumen
- Rated power: 5 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8718699723088
- Net weight: 0.042 kg
- Gross weight: 0.068 kg
- Height: 9.600 cm
- Length: 4.700 cm
- Width: 9.300 cm
- Material number (12NC): 929002275379



Issue date: 2021-09-07
Version: 0.78

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com