

PHILIPS

Ceiling light

myLiving

CL505

Silver

RF Dimming

8718699748395



Set your desired ambiance at your fingertips

Philips LED luminaires provide light that is designed for the comfort of your eyes

Ambient light effect

- Soft night light

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Tunable color temperature
- Remote control included for your convenience
- High performance, durable diffuser for uniform lighting and reduced glare.
- 4 pre-set scenes
- Auto shutdown after 60 mins
- Link up to 3 pcs with one remote control

Highlights

Soft night light

Help your loved ones drop off to a sleep in soft night light.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Tunable color temperature

Shift from crisp white light for focus to a warm yellow light for relaxation.

Remote control included for your convenience

Choose different light colors, dimming levels and select between different pre-set light settings.

High performance, durable diffuser for uniform lighting and reduced glare.

This diffuser distributes soft light evenly across your rooms.

4 pre-set scenes

Enjoy different ambiances with the convenience of pre-set light scenes for every occasion.

Auto shutdown after 60 mins

When sleep mode is on, the light will automatically go out after 60 minutes. No more getting up in the middle of the night just to switch the light off.

Link up to 3 pcs with one remote control

Control all lighting in your room without having to get up with this powerful and smart remote control.

Specifications

Design and finishing

- Color: silver
- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions & weight

- Height: 8.5 cm
- Length: 39.5 cm
- Net weight: 0.74 kg
- Width: 39.5 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 395 mm
- Total lumen output fixture: 2000
- Light color: 2700-6500
- Mains power: 220-240
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 23
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8718699748395
- Net weight: 0.300 kg
- Gross weight: 1.020 kg
- Height: 8.500 cm
- Length: 46.000 cm
- Width: 46.000 cm
- Material number (12NC): 915005774807



Issue date: 2021-06-04
Version: 0.59

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com