

PHILIPS

Spot

LED

4W-40W

R7S

Cool White



8718699761189



Experience warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Cool, white light

Choose for a sustainable solution

- Saves up to 80% energy

Light beyond illumination

- A simple LED for everyday use

Highlights

Cool, white light



This lamp has a colour temperature of 4000K providing you with an extra cool, fresh and crisp light.

Saves up to 80% energy



Enjoy the energy savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A simple LED for everyday use



The Philips everyday LED is the perfect lamp for your basic lighting needs. It provides the beautiful light and dependable performance that you expect from LED at an affordable price.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional reflector
- Socket: R7S
- Technology: LED

Lamp dimensions

- Height: 7.8 cm
- Weight: 0.01 kg
- Width: 1.45 cm

Durability

- Average life (at 2.7 hrs/day): 10 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 h
- Number of switch cycles: 5,000

Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 500 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

Miscellaneous

- EyeComfort: No

Other characteristics

- Lamp current: 20.5 mA
- Efficacy: 125 lm/W

Packaging information

- EAN: 8718699761189
- EOC: 871869976118900
- Product title: LEDClassic 40W R7S 78mm CW ND SRT4

Power consumption

- Power factor: 0.8
- Voltage: 220–240 V
- Wattage: 4 W
- Wattage equivalent: 40 W

Product dimensions and weight

- Length: 7.8 cm

Rated values

- Rated lifetime: 10,000 h
- Rated luminous flux: 500 lm
- Rated power: 4 W

Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-08
Version: 0.152

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com