

# PHILIPS

## Candle & Lustre

LED

6.5W-60W

E14

Cool White



8718699762872



## Bright LED lighting with excellent light quality

Philips LED frosted candles provide a soft, diffuse light effect and an exceptionally long life. With a pure and elegant design, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### High-quality light

- Designed for the comfort of your eyes

### Create the right light for your home

- Perfect for decorative fixtures

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Technology: LED
- Type of glass: Frosted

## Lamp dimensions

- Height: 8 cm
- Weight: 0.021 kg
- Width: 4.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 4000 K
- Light Colour Category: Cool White
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 840 | CCT of 4000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 50 mA
- Efficacy: 124 lm/W

## Packaging information

- EAN: 8718699762872
- EOC: 871869976287200
- Product title: LED classic 60W E14 CW P45 FR ND 1PF/10

## Power consumption

- Power factor: 0.55
- Voltage: 220–240 V
- Wattage: 6.5 W
- Wattage equivalent: 60 W
- Energy efficiency label (EEL): E

## Product dimensions and weight

- Length: 8 cm

## Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 6.5 W

## Technical specifications

- Frequency: 50–60 Hz

## The bulb

- Colour consistency: 6

**Packaging dimensions and weight**  
**[LED classic 60W E14 CW P45 FR ND**  
**SRT4]**

- EAN/UPC - product: 8718699762872
- Net weight: 0.018 kg
- Gross weight: 0.037 kg
- Height: 12.700 cm
- Length: 5.300 cm
- Width: 6.300 cm
- Material number (12NC):  
929002028828

**Packaging dimensions and weight**  
**[LED classic 60W E14 CW P45 FR ND**  
**1PF/10]**

- EAN/UPC - product: 8718699762872
- Net weight: 0.018 kg
- Gross weight: 0.037 kg
- Height: 12.700 cm
- Length: 5.300 cm
- Width: 6.300 cm
- Material number (12NC):  
929002028855



Issue date: 2023-11-08  
Version: 0.394

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)