

PHILIPS

Filament Bulb Frosted
200W A95 E27

LED

23 W-200 W

E27

Warm White



8718699764630



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Create the right light for your home

- A simple LED for everyday use

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up

your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Bulb material: Glass

Lamp dimensions

- Height: 16.5 cm
- Width: 9.5 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 3452 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature: 2700 K
- Luminous efficacy (rated) (nom.): 150.00 lm/W
- Luminous Flux: 3,452 lm
- Stroboscopic effect: 0.4

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 150 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699764630
- EOC: 871869976463000
- Product title: LED classic 200W A95 E27 WW FR ND 1PF

Power

- Power Factor (Fraction): 0.51

Power consumption

- Power factor: 0.51
- Voltage: 220–240 V
- Wattage: 23 W
- Wattage equivalent: 200 W
- Energy efficiency label (EEL): D
- Power Consumption: 23 W

Product dimensions and weight

- Length: 16.5 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 374908
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Cap base: E27

The bulb

- Colour consistency: 6

Packaging dimensions and weight

- EAN/UPC – product: 8718699764630
- Net weight: 0.1 kg
- Gross weight: 0.16 kg
- Height: 22.6 cm
- Length: 10.2 cm
- Width: 13 cm
- Material number (12NC): 929002372901



Issue date: 2024-02-06
Version: 0.308

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com