

PHILIPS

Lamp (Dimmable)

LED

7W-60W


E27

Warm Glow

Dimming



8718699770488



A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

High-quality light

- Designed for the comfort of your eyes

Create the right light for your home

- Perfect for decorative fixtures

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Perfect for decorative fixtures

Modern lighting in Philips LED globes for use in decorative fixtures, such as ceiling fans and vanity strips.

Specifications

Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Technology: LED
- Type of glass: Clear

Lamp dimensions

- Height: 14.2 cm
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 270 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2700-2200 K
- Light Colour Category: Warm Glow
- Nominal luminous flux: 806 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 927-922 | CCT of 2700K-2200K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 40 mA
- Efficacy: 115 lm/W

Packaging information

- EAN: 8718699770488
- EOC: 871869977048800
- Product title: LED classic 60W G93 E27 CL WGD90 1PF/4

Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W

Product dimensions and weight

- Length: 14.2 cm

Rated values

- Rated beam angle: 270 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 806 lm
- Rated power: 7 W

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699770488
- Net weight: 0.060 kg
- Gross weight: 0.113 kg
- Height: 18.200 cm
- Length: 10.200 cm
- Width: 13.000 cm
- Material number (12NC): 929002393001



Issue date: 2023-11-07
Version: 0.246

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com