

# PHILIPS

Candle 15W T25 E14

LED

1.7W-15W

E14

Warm White



8718699771935



## State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra warm light, an exceptionally long life, and immediate, significant energy savings. With its flame color temperature, this light bulb is the perfect choice for a cozy atmosphere.

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### Choose for a sustainable solution

- Long life bulbs - Lasts up to 15 years

### Light beyond illumination

- For use in refrigerators and freezers

# Highlights

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## Special purpose appliance bulb

Philips refrigerator bulbs can be used in refrigerators, freezers, and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips refrigerator bulb for a long, useful life.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional luster
- Socket: E14
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Plastic

## Bulb dimensions

- Height: 5.9 cm
- Width: 2.5 cm

## Design and finishing

- Material: Plastic

## Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 150 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 827 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 88.00 lm/W
- Luminous Flux: 150 lm
- Stroboscopic effect visibility measure (SVM): 0.4

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Efficacy: 88 lm/W
- EU RoHS compliant: Yes

**Packaging information**

- EAN: 8718699771935
- EOC: 871869977193501
- Product title: LED 15W T25 E14 WW  
FR ND RF 1SRT6

**Power**

- Power Factor (Fraction): 0.4

**Power consumption**

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 1.7 W
- Wattage equivalent: 15 W
- Energy Efficiency Label (EEL): F
- Power Consumption: 1.7 W

**Product dimensions and weight**

- Length: 5.9 cm

**Rated values**

- Rated lifetime: 15,000 h

**Technical specifications**

- Frequency: 50–60 Hz
- EPREL Registration Number: 391879
- Flux measurement reference: Sphere
- Dimmable: No
- Flickering value (PstLM) – Flickering  
value as per EN 61000-3-3: 1
- Line Frequency: 50 to 60 Hz
- Cap-Base: E14

**The bulb**

- Color consistency: 6

**Packaging dimensions & weight**

- EAN/UPC – product: 8718699771935
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC):  
929001325755



Issue date: 2024-02-07  
Version: 0.258

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)