

PHILIPS

Candle 15W T25 E14

LED

1.7W-15W

E14

Warm White



8718699771935



State-of-the-art LED light bulb for the home

This Philips LED light bulb provides a beautiful, extra-warm light, an exceptionally long life and immediate, significant energy savings. With its flame colour temperature, this light bulb is the perfect choice for a cosy atmosphere.

Choose a simple replacement for your old lamps

- Similar shape and size as standard incandescent bulbs

Choose for a sustainable solution

- Long-life bulbs – Last up to 15 years

Light beyond illumination

- For use in fridges and freezers

Highlights

Replaces lustre incandescents

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

Special-purpose appliance bulb

Philips fridge bulbs can be used in fridges, freezers and similar places subject to low operating temperatures. Easily replace your appliance bulbs with a Philips fridge bulb for a long, useful life.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E14
- Type of glass: Frosted
- Lamp Finish: Frosted
- Bulb material: Plastic

Lamp dimensions

- Height: 5.9 cm
- Width: 2.5 cm

Design and finishing

- Material: Plastic

Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 240 degree(s)
- Colour rendering index (CRI): 80
- Colour temperature: 2700 K
- Nominal luminous flux: 150 lm
- Warm-up time to 60% light: 0.5 s
- Colour Code: 827 | CCT of 2700K
- Correlated Colour Temperature: 2700 K
- Luminous efficacy (rated) (nom.): 88.00 lm/W
- Luminous Flux: 150 lm
- Stroboscopic effect: 0.4

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 88 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699771935
- EOC: 871869977193502
- Product title: LED 15W T25 E14 WW
FR ND RF 1SRT6 UK

Power

- Power Factor (Fraction): 0.4

Power consumption

- Power factor: 0.4
- Voltage: 220–240 V
- Wattage: 1.7 W
- Wattage equivalent: 15 W
- Energy efficiency label (EEL): F
- Power Consumption: 1.7 W

Product dimensions and weight

- Length: 5.9 cm

Rated values

- Rated lifetime: 15,000 h

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 391879
- Dimmable: No
- Flickering value (PstLM): 1
- Line Frequency: 50 to 60 Hz
- Cap base: E14

Packaging dimensions and weight

- EAN/UPC – product: 8718699771935
- Net weight: 0.01 kg
- Gross weight: 0.02 kg
- Height: 12.7 cm
- Length: 2.5 cm
- Width: 6.3 cm
- Material number (12NC):
929001325796



Issue date: 2024-02-07
Version: 0.260

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com