

# PHILIPS

Lamp (Dimmable)

LED

3.5W-15W

E27

Flame

Dimming



8718699774912



## A light bulb like no other

Philips LED flame candles provide a beautiful, warm light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### High-quality light

- Designed for the comfort of your eyes

### Create the right light for your home

- Perfect for decorative fixtures

### Light beyond illumination

- Dims to a warm glow

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience

flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Perfect for decorative fixtures



Contemporary lighting in Philips LED lustres for use in decorative fixtures such as chandeliers, ceiling fans, vanity strips and post lights.

## Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non-directional lustre
- Socket: E27
- Technology: LED
- Type of glass: Transparent Amber

## Lamp dimensions

- Height: 8 cm
- Weight: 0.024 kg
- Width: 4.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2000 K
- Light Colour Category: Flame
- Nominal luminous flux: 136 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 820 | CCT of 2000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 22 mA
- Efficacy: 38 lm/W

## Packaging information

- EAN: 8718699774912
- EOC: 871869977491200
- Product title: LED classic 15W P45 E27 GOLD SP D SRT4

#### Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 3.5 W
- Wattage equivalent: 15 W

#### Product dimensions and weight

- Length: 8 cm

#### Rated values

- Rated lifetime: 15,000 h
- Rated luminous flux: 136 lm
- Rated power: 3.5 W

#### Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-07  
Version: 0.225

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)