

# PHILIPS

Lamp (Dimmable)

LED

7.2 W-50 W


E27

Flame

Dimming



8718699782511



## A light bulb like no other

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

### High-quality light

- Designed for the comfort of your eyes

### Create the right light for your home

- Perfect for decorative fixtures

### Light beyond illumination

- Dims to a warm glow

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

## Dims to a warm glow

With this dimmable bulb, you can dim from a 2200k warm light to a 2700K light. The more you dim, the warmer the light.

## Perfect for decorative fixtures

Modern lighting in Philips LED globes for use in decorative fixtures, such as ceiling fans and vanity strips.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non directional globe
- Socket: E27
- Technology: LED
- Type of glass: Amber

## Lamp dimensions

- Height: 18 cm
- Weight: 0.102 kg
- Width: 12.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 270 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 80
- Colour temperature: 2200 K
- Light Colour Category: Flame
- Nominal luminous flux: 650 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 822 | CCT of 2200K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 45 mA
- Efficacy: 90 lm/W

## Packaging information

- EAN: 8718699782511
- EOC: 871869978251100
- Product title: LEDclassic 50W G120 E27 2200KGOLD RF 1PF

## Power consumption

- Power factor: 0.7
- Voltage: 220-240 V
- Wattage: 7.2 W
- Wattage equivalent: 50 W

## Product dimensions and weight

- Length: 18 cm

## Rated values

- Rated beam angle: 270 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 650 lm
- Rated power: 7.2 W

## Technical specifications

- Frequency: 50-60 Hz



Issue date: 2023-11-07  
Version: 0.256

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)