

# PHILIPS

Reflector  
(Dimmable)

LED

4.2W-60W

E27

Warm White

Dimming



8718699787660



## Durable LED accent lighting with a focused beam

This directional LED lamp provides a focused beam of warm, white light and is an excellent replacement for traditional reflector lamps

### High quality light

- True incandescent-like warm white light

### Create the right light for your home

- Perfect for accent lighting

### Light beyond illumination

- Dimmable

# Highlights

## Incandescent-like warm white



This bulb has a color temperature of 2700K, providing you with a warm, tranquil atmosphere, perfect for relaxing. This 2700K light is ideal for home lighting design

## Perfect for accent lighting



Modern lighting with a familiar wide angle light output (36 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in

kitchens, kitchen island lighting, living rooms and dining rooms.

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: E27
- Technology: LED

## Bulb dimensions

- Height: 11.2 cm
- Weight: 0.16 kg
- Width: 8 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 36 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 345 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 25 mA
- Efficacy: 82 lm/W

## Packaging information

- EAN: 8718699787660
- EOC: 871869978766000
- Product title: LED CLA 60W R80 E27 WW 36D D 1PF/4

## Power consumption

- Power factor: 0.8
- Voltage: 220-240 V
- Wattage: 4.2 W
- Wattage equivalent: 60 W

## Product dimensions & weight

- Length: 11.2 cm

## Rated values

- Rated beam angle: 36 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 345 lumen
- Rated peak intensity: 620 cd
- Rated power: 4.2 W

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 8718699787660
- Net weight: 0.160 kg
- Gross weight: 0.182 kg
- Height: 11.300 cm
- Length: 7.800 cm
- Width: 7.800 cm
- Material number (12NC):  
929002428166



Issue date: 2021-11-29  
Version: 0.21

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)