

PHILIPS

Bulb

LED

17W-145(145W GLS, 35W CFL)W

B22

Cool Daylight

8719514252752



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

High quality LED light that lasts for decades

- Switch to extra brightness

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

EyeComfort with concaved optical design

This bulb brings a comfortable, energy-efficient and long-lasting lamp with a concave design that casts a wide beam for extra brightness.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: T70
- Socket: B22
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 12.42 cm
- Weight: 0.068 kg
- Width: 7 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 2350 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 170 mA
- Efficacy: 138 lm/W

Packaging information

- EAN: 8719514252752
- EOC: 871951425275200
- Product title: LEDBright 17W B22 6500K 230V 1PF/6 AU

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 17 W
- Wattage equivalent: 145 W
- Energy Efficiency Label (EEL): 5 Star for UAE, 3 Tick for SG

Product dimensions & weight

- Length: 12.42 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 2350 lumen
- Rated power: 17 W

Technical specifications

- Frequency: 50 to 60

Packaging dimensions and weight

- EAN/UPC - product: 8719514252752
- Net weight: 0.067 kg
- Gross weight: 0.092 kg
- Height: 16.000 cm
- Length: 7.000 cm
- Width: 7.000 cm
- Material number (12NC): 929002435119



Issue date: 2020-11-26
Version: 0.138

© 2020 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com