

PHILIPS

Bulb

LED

13W-104(104W GLS, 24W CFL)W

E27

Cool Daylight

8719514252875



Bright LED lighting with excellent light quality

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

High quality LED light that lasts for decades

- Switch to extra brightness

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

EyeComfort with concaved optical design

This bulb brings a comfortable, energy-efficient and long-lasting lamp with a concave design that casts a wide beam for extra brightness.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: T60
- Socket: E27
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 11.05 cm
- Weight: 0.054 kg
- Width: 6 cm

Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Light Color Category: Cool Daylight
- Nominal luminous flux: 1600 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 130 mA
- Efficacy: 123 lm/W

Packaging information

- EAN: 8719514252875
- EOC: 871951425287500
- Product title: LEDBright 13W E27 6500K 230V 1CT/12 APR

Power consumption

- Power factor: 0.5
- Voltage: 220–240 V
- Wattage: 13 W
- Wattage equivalent: 104 W

Product dimensions & weight

- Length: 11.05 cm

Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 1600 lumen
- Rated power: 13 W

Technical specifications

- Frequency: 50–60 Hz

Bulb characteristics

- EAN/UPC - product: 8719514252875
- Rated beam angle: 150 degree(s)
- Height: 11.05 cm
- Average life (at 2.7 hrs/day): 15 year(s)
- Beam angle: 150 degree(s)
- Lamp current: 130 mA
- Net weight: 0.044 kg
- Rated lifetime: 15,000 hour(s)
- Intended use: Indoor
- Weight: 0.054 kg
- Lumen maintenance factor: 70%
- Color consistency: 6SDCM
- Gross weight: 0.063 kg
- EAN: 8719514252875
- Rated luminous flux: 1600 lumen
- Lamp shape: T60
- Width: 6 cm
- Color rendering index (CRI): 80
- Height: 11.800 cm
- EOC: 871951425287500
- Socket: E27
- Number of switch cycles: 50,000
- Color temperature: 6500 K
- EyeComfort: Yes
- Length: 6.200 cm
- Product title: LEDBright 13W E27
6500K 230V 1CT/12 APR
- Power factor: 0.5
- Rated power: 13 W
- Technology: LED
- Light Color Category: Cool Daylight
- Width: 6.200 cm
- Voltage: 220-240 V
- Type of glass: Frosted
- Nominal luminous flux: 1600 lumen
- Material number (12NC):
929002433307
- Wattage: 13 W
- Length: 11.05 cm
- Starting time: <0.5 s
- Wattage equivalent: 104 W
- Warm-up time to 60% light: Instant
full light
- Color Code: 865 | CCT of 6500K
- Frequency: 50-60 Hz



Issue date: 2022-06-12
Version: 0.170

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.