

PHILIPS

Candle

LED

4W-40W

B22

White

8719514256217



Clear LED candle bulbs add a sparkle to your home

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and off, this light bulb is the perfect match for chandelier fixtures with small (E27) fittings.

High quality light

- Long life bulb - Lasts up to 10 years

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Light beyond illumination

- A simple LED for everyday use
- Instant on

Designed to be seen, looks good on and off

- Looks good on and off

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on

Looks good on and off



"These beautiful lamp with visible filament add a sense of style and nostalgia to any room. Looks good on and off."

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: C37
- Socket: E27
- Technology: LED
- Type of glass: Clear

Bulb dimensions

- Height: 10.6 cm
- Weight: 0.036 kg
- Width: 3.4 cm

Durability

- Average life (at 2.7 hrs/day): 10 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,000 hour(s)
- Number of switch cycles: 5,000

Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: White
- Nominal luminous flux: 400 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 35 mA
- Efficacy: 100 lm/W

Packaging information

- Product family: LED
- EAN: 8719514256217
- EOC: 871951425621700
- Product title: Led Clear Candle 4W,400lm,3000k ,E27

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 4 W
- Wattage equivalent: 40 W

Product dimensions and weight

- Length: 10.7 cm

Rated values

- Rated luminous flux: 400 lumen
- Rated power: 4 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC – product: 8719514256217
- Net weight: 36.000 g
- Gross weight: 46.000 g
- Height: 108.000 mm
- Length: 36.000 mm
- Width: 36.000 mm
- Material number (12NC): 929002420113



Issue date: 2023-11-08
Version: 0.149

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com