

PHILIPS

Linear tube

LED

2.2W-35W

S14S

Warm White



8719514263567



Bright LED lighting with excellent light quality

This Philips LED tubular S14D provides an exceptionally long life and significant energy savings. With its warm white colour temperature, this tube is the perfect long-lasting replacement for your linear fluorescent (TL) tubes.

High quality light

- Light all around

Highlights

Light all around

Thanks to its innovative but vintage design shape, this LED bulb prevents

the shadow that normally appears at the beam spread edge. The result? Natural warm white light all around.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Other
- Socket: S14S
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 30 cm
- Weight: 0.085 kg
- Width: 3 cm

Durability

- Average life (at 2.7 hrs/day): 30 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 30,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Application: Corridor, Industry, Storage, Car Park, Butcher, Bakery, Retail/hospitality
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 250 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 22 mA
- Efficacy: 113 lm/W

Packaging information

- EAN: 8719514263567
- EOC: 871951426356700
- Product title: LED 2.2W 300mm S14S WW ND 1CT/4

Power consumption

- Power factor: 0.4
- Voltage: 220-240 V
- Wattage: 2.2 W
- Wattage equivalent: 35 W
- Energy Efficiency Label (EEL): E

Product dimensions & weight

- Length: 30 cm

Rated values

- Rated beam angle: 140 degree(s)
- Rated lifetime: 30,000 hour(s)
- Rated luminous flux: 250 lumen
- Rated power: 2.2 W

Technical specifications

- Frequency: 50-60 Hz

The bulb

- Color consistency: 6

Packaging dimensions and weight

- EAN/UPC - product: 8719514263567
- Net weight: 0.100 kg
- Gross weight: 0.128 kg
- Height: 33.500 cm
- Length: 3.300 cm
- Width: 5.100 cm
- Material number (12NC): 929002444201



Issue date: 2022-01-20
Version: 0.235

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com