

# PHILIPS

Spot (Dimmable)

LED

5W-50W

GU10

Warm White

Dimming

8719514274099



## Durable LED accent lighting with a focused bright beam

This Philips LED spot provides a dimmable, focused bright beam, an exceptionally long life, and significant energy savings. This spot is the perfect long-lasting replacement for 50W spots with a GU10 cap.

### High quality light

- Cool, energizing light

### Choose for a sustainable solution

- Saves up to 80% Energy

### Create the right light for your home

- Perfect for accent lighting and general purpose lighting

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## 60° beam - spot



Modern lighting with a familiar extra wide angle light output (60 degrees), this LED spot is suitable for both accent lighting and general purpose lighting. It can be used in recessed cans and track light fixtures, and is ideal for use in kitchens, kitchen island lighting, living rooms and dining rooms.

# Specifications

## Bulb characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Directional reflector
- Socket: GU10
- Technology: LED

## Bulb dimensions

- Height: 5.4 cm
- Weight: 0.05 kg
- Width: 5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 60 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Warm White
- Nominal luminous flux: 405 lumen
- Starting time: 0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 25 mA
- Efficacy: 81 lm/W

## Packaging information

- EAN: 8719514274099
- EOC: 871951427409900
- Product title: LEDClassic 5-50W GU10 830 60D D 1PF/10

#### Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 5 W
- Wattage equivalent: 50 W

#### Product dimensions and weight

- Length: 5.4 cm

#### Rated values

- Rated beam angle: 60 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 405 lumen
- Rated peak intensity: 450 cd
- Rated power: 5 W

#### Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-08  
Version: 0.28

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)