

PHILIPS

Recessed spot light

myLiving

Thin Trim Dimmable COB

White



8719514278165



Control your light. Experience with ease.

Thin Trim Dimmable COB has minimalistic trim which blends well with the ceiling. This COB is dimmable with the help of dimmer or can be used in track dimming; giving consumer a choice to change the intensity of light which goes with the mood

Light effect

- Bright and focused beam

Premium quality

- Durable and impact resistant die-cast aluminum housing

Control

- Dimmable with wall switch

Durability

- Long life span up to 30,000 hours

Highlights

Bright and focused beam

Focus light on objects, a dining table or other interiors to draw attention to particular stylings.

Durable and impact resistant die-cast aluminum housing

The die-cast aluminum housing of this item adds to a cultivated and refined contemporary atmosphere.

Dimmable with wall switch

Lets you easily dim lights to the required level of brightness.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Design and finishing

- Color: White
- Material: metal

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: No

Light characteristics

- Beam angle: 36 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Living- & Bedroom

Product dimensions & weight

- Cut out length: 6.8 cm
- Cut out width: 6.8 cm
- Height: 10 cm
- Length: 7.5 cm
- Net weight: 0.13 kg
- Width: 7.5 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 35,000 hour(s)
- Diameter: 75 mm
- Total lumen output fixture: 760
- Light color: 4000
- Mains power: 220-240
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 12
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8719514278165
- Net weight: 0.210 kg
- Gross weight: 0.240 kg
- Height: 12.200 cm
- Length: 10.400 cm
- Width: 7.800 cm
- Material number (12NC): 929001951961



Issue date: 2021-05-04
Version: 0.24

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com