

# PHILIPS

Candle (Dimmable)

LED

4.5W-40W

B22

Warm Glow

Dimming



8719514290747



## Experience dimmable, warm white LED light

Philips LED flame candles provide a beautiful, warm light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

### High-quality light

- Designed for the comfort of your eyes

### Choose for a sustainable solution

- Better for your wallet and your planet

### High-quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go

easy on the eyes, and create the perfect ambience for your home.

## Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Characteristics

- Dimmable: Yes
- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: B22
- Technology: LED
- Type of glass: Clear

## Lamp dimensions

- Height: 9.1 cm
- Weight: 0.02 kg
- Width: 3.5 cm

## Durability

- Average life (at 2.7 hrs/day): 15 a
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

## Light characteristics

- Beam angle: 270 degree(s)
- Colour consistency: 6SDCM
- Colour rendering index (CRI): 90
- Colour temperature: 2700-2200 K
- Light Colour Category: Warm Glow
- Nominal luminous flux: 470 lm
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Colour Code: 927-922 | CCT of 2700K-2200K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 30 mA
- Efficacy: 104 lm/W

## Packaging information

- EAN: 8719514290747
- EOC: 871951429074700
- Product title: LED classic 40W B35 B22 CL WGD90 SRT4

#### Power consumption

- Power factor: 0.7
- Voltage: 220–240 V
- Wattage: 4.5 W
- Wattage equivalent: 40 W

#### Product dimensions and weight

- Length: 9.1 cm

#### Rated values

- Rated beam angle: 270 degree(s)
- Rated lifetime: 15,000 h
- Rated luminous flux: 470 lm
- Rated power: 4.5 W

#### Technical specifications

- Frequency: 50–60 Hz



Issue date: 2023-11-07  
Version: 0.20

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)