



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering Guide

Example: BUL1 A S

Product Code	BUL1	Composite Bullyte
Finish	A G H	Black Verde Bronze
Shroud	S L	Short Shroud Long Shroud

*1 US: 50 Watt / CAN: 20 Watt

Specifications

HOUSING:

One-piece injection molded ULTEM® High Performance Polymer composite. Fully-adjustable swivel arm with vibration-proof locking teeth. Fully rotatable shroud, gasketed, ULTEM® High Performance Polymer composite. Fasteners are 300 series stainless steel. ½" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Composite is textured, pressure formed, molded-in-color.

OPTICAL ASSEMBLY:

Clear tempered glass lens.

LAMPING:

50W maximum MR16 bi-pin lamp. Covered MR16 are recommended to protect lamps inner capsule. Lower wattage lamps are acceptable. Lamp is not included.

ELECTRICAL ASSEMBLY:

Bi-pin socket type (GU5.3) with 250° C high temperature teflon coated wire leads. The wires are permanently fused to the clip. Stainless Steel lamp clip is designed to prevent arching of bi-pin and also acts as a heat sync to keep heat away from the socket. Electrical internal connectors are stainless steel 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

WARRANTY:

Ten-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width:

3 7/8" (98mm)

Length:

8 1/2" (216mm)

Max. Weight:

1.45 lb

