
## **LED HIGHBAY**

## **Installation Instruction**

Philips Lighting



TYPE : BY325P

LAMP : LED

VOLTAGE : 240 V, 50 Hz

IP CLASSIFICATION : IP 66

NET WEIGHT : 5.8 Kg.

MAX. PROJECTED AREA: 0.1 m<sup>2</sup>

CCT : 6500 K

APPLICATION : LED HIGHBAY

IP-66


Ta-45






## **Dimensions**

**Indoor Luminaire** 









Follow the below mention sequence for


assembly of Mounting bracket with four


M6 screws, Spring washer and flat SS


washer.

















9

## **CAUTION**

- 1. Ensure L-N-E is connected in right manner.
- 2. Ensure 3 core CABLE for Connections(Outer diameter 8-12mm multi strand 1.2 sq. mm thk.)
- 3. 3 Core cable should be properly connected with ground & pass through cable clamp properly.
- 4. Ensure mounting bracket assembly to be fix by four M6 screws at 10-12 N-m torque.
- 5. Ensure I bolt mounting properly with specified load(safety issue)
- 6. Luminaire must be brought down from the mounting position for maintenance.

FAILURE OF PRODUCT DUE TO NON COMPLIANCE TO ANY OF THE ABOVE, VOIDS WARRANTY OF PRODUCT

Spring Washer

SS Washer