

DHILIPS GreenSpace Accent Cardanic RS343B			
$\begin{array}{c} \textbf{CC} \\ \textbf{IP20} \\ \textbf$			Max. 40°C Vin. 10°C
Model Lumen package Color Temperature [K] LED17S 827/830/840/PW930 RS343B LED19S FMT/ROSE LED27S 827/830/840/CH/FR/PW930/FMT/ROSE/PC930 LED39S 827/830/840/PW930/PC930 LED49S 827/830/840/PW930/PC930	1,1 1,1 1,1 1,1 1,1 1,1 1,1 1,1	Prod	luct info
Main dimensions (in mm)		PSU-E	
			Printed in





LED17S/827,830,840,PW930		LED19S/FMT,ROSE LED27S/PW930,ROSE/PC930		LED275/827,830,840,CH,FR		LED395/827,830,840		LED27S/FMT LED39S/PW930/PC930 LED49S/827,830,840	
20W PSU		36W PSU		28W PSU		34W PSU		50W PSU	
Ipeak[A]	18,6	Ipeak[A]	18,6	Ipeak[A]	6,1	Ipeak[A]	11	Ipeak[A]	18
Tref[us]	240	Tref[us]	240	Tref[us]	310	Tref[us]	306	Tref[us]	250
МСВ	Max products [pcs]*	МСВ	Max products [pcs]*	МСВ	Max products [pcs]*	МСВ	Max products [pcs]*	МСВ	Max products [pcs]*
B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤34	B-16A type B	≤30
				PSU-E					
LED175/827,830,840,PW930		LED19S/FMT,ROSE LED27S/827,830,840,PW930,CH,FR, ROSE/PC930 LED39S/827,830,840		LED275/FMT LED395/PW930/PC930 LED495/827,830,840		Imax	I mains (A)		
20W PSD-VLC-E		36W PSD-VLC-E		50W PSD-VLC-E		Παλ			
Ipeak[A]	20,4	Ipeak[A]	20,4	Ipeak[A]	24,9				
Tref[us]	195	Tref[us]	195	Tref[us]	186				
МСВ	Max products [pcs]*	МСВ	Max products [pcs]*	МСВ	Max products [pcs]*	max /	2		
B-16A type B	≤24	B-16A type B	≤24	B-16A type B	≤27				
PSD-VLC-E									I nom.
							Tref		Time (us)

material.

The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
 Caution, risk of electric shock. The light source of this luminaire is not replaceable, when the light source

reaches its end of life the whole luminaire shell be replaced. The driver shall only be replaced by the manufacturer or his service agent or a smiliar qulified person.





© 2018 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject tochange. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.. All other trademarks are owned by Signify Holding or their respective owners.

Signify Holding. The Netherlands