



Applicable part numbers for all InstantFit lamps:

452011	452029	452037	452045	452052	452060	452078	452086	453589	453597	453605	453613	456897	456905
456913	456921	463133	463141	463158	456566	456574	456590	456608	456616	456624	452664	452672	452680
452698	456632	456640	456657	458406	458414	458422	458430	458364	458372	458380	458398	464206	464214
464222	464230	464248	464255	464263	464271	463117	463125						

InstantFit drivers ^{1,2}		8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15W 2100lm (4ft.)	16.5W 2500lm (4ft.)	17W 2100 lm (4ft. Glass)	16.5W 2100lm (U- Bent)⁵
		452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	463133, 463141, 463158	456566, 456574 456590, 456608 456616, 456624	452664, 452672, 452680, 452698
Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Philips Advance	ICN-2P16-TLED-N	System Certified	System Certified	System Certified	System Certified	System Certified		System Certified
Philips Advance	ICN-4P16-TLED-N	System Certified	System Certified	System Certified	System Certified	System Certified		

Systems on this page are:



See footnotes on Page 8.

T8	instant-start
hal	lasts1

T8 instant-start ballasts ¹		8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15 W 2100 lm (4ft.)	16.5W 2500lm (4ft.)	17W 2100 lm (4ft. Glass)	16.5W 2100lm (U- Bent) ⁵
		452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	463133, 463141, 463158	456566, 456574 456590, 456608 456616, 456624	452664, 452672, 452680, 452698
Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Philips Advance	ICN-1P32-N	System Certified	System Certified	System Certified	System Certified			
Philips Advance	ICN-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	ICN-3P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	ICN-4P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-1P32-N	Not Recommended	System Certified	System Certified	Not Recommended	Not Recommended	Not Recommended	Not Recommended
Philips Advance	IOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-4P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-4P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-1P32-HL-N	System Certified	System Certified	System Certified			System Certified	
Philips Advance	IOPA-2P32-HL-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	IOPA-3P32-HL-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	IOPA-4P32-HL-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-1P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-2P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-3P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-4P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-1P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-2P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-2P32-LW-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	GOPA-3P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	GOPA-4P32-LW-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	
Philips Advance	RES-2P32-N	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-2P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Advance	REB-4P32-SC	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	

See footnotes on Page 8.

T8	instant-start
hal	lasts1

T8 instant-start		8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15 W 2100 lm (4ft.)	16.5W 2500lm (4ft.)	17W 2100 lm (4ft. Glass)	16.5W 2100lm (U- Bent)⁵
ballasts ¹		452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	463133, 463141, 463158	456566, 456574 456590, 456608 456616, 456624	452664, 452672, 452680, 452698
Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Fulham Co. Inc	WH3-120-L	System Certified	System Certified	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WH3-277-L	System Certified	System Certified	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WH5-120-L	System Certified	System Certified	System Certified	System Certified		System Certified	
Fulham Co. Inc	WH5-277-L	System Certified	System Certified	System Certified				
Fulham Co. Inc	WHSG1-UNV-T8-IS	Not Recommended	System Certified	System Certified	System Certified		System Certified	
Fulham Co. Inc	WHSG2-UNV-T8-IS	System Certified	System Certified	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WHSG2-UNV-T8-LB		System Certified	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WHSG3-UNV-T8-IS	Not Recommended	Not Recommended	System Certified	System Certified		System Certified	,
Fulham Co. Inc	WHSG3-UNV-T8-LB	Not Recommended	Not Recommended	System Certified			-	
Fulham Co. Inc	WHSG3-UNV-T8-HB	Not Recommended	Not Recommended	System Certified	System Certified		System Certified	
Fulham Co. Inc	WH42-UNV-L	System Certified	System Certified	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WH43-UNV-L	Not Recommended	Not Recommended	System Certified	System Certified		System Certified	System Certified
Fulham Co. Inc	WH44-UNV-L	Not Recommended	Not Recommended	System Certified	System Certified		System Certified	System Certified
Fulham Co.Inc / Leviton	Zipline (361RC-Z03)	Not Recommended	Not Recommended	System Certified				·
General Electric	GE-132-MV-N		Certified	Certified	Certified	Certified	Certified	
General Electric	GE-232-MV-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N	Certified	Certified	Certified	Certified	Certified	Certified	
General Electric	GE-232-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE-332-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	
General Electric	GE-432-MV-N-DIY	Certified	Certified	Certified	Certified	Certified	Certified	
General Electric	GE232MAX-N/ULTRA	Certified	Certified	Certified	Certified	Certified	Not Recommended	Certified
General Electric	GE432MAX-N/ULTRA	Not Recommended	Not Recommended	Not Recommended	Certified	Certified	Certified	
General Electric	GE232MAX-L/ULTRA	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE332MAX-L/ULTRA	Not Recommended	Certified	Certified	Certified	Certified	Certified	
General Electric	GE132MAX-H/ULTRA		Certified	Certified	Certified	Certified	Certified	
General Electric	GE232MAX-H/ULTRA	Certified	Certified	Certified	Certified	Not Recommended	Not Recommended	Certified
General Electric	GE332MAX-H/ULTRA	Not Recommended	Not Recommended	Not Recommended	Certified	Certified	Certified	
General Electric	GE432MAX-H/ULTRA	Certified	Certified	Certified	Certified	Certified	Certified	
General Electric	GE232MAX347-N	Certified	Certified	Certified		Certified		Certified
General Electric	GE432MAX347-N	Certified	Certified	Certified	Certified	Certified	Certified	
General Electric	GE232-120RES-DIY	Certified	Certified	Certified	Certified	Certified	Certified	Certified
General Electric	GE432-120RES-DIY	Certified	Certified	Certified	Certified	Certified	Certified	

T8	instant-start
hal	lasts1

T8 instant-start ballasts¹		8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15 W 2100 lm (4ft.)	16.5W 2500lm (4ft.)	17W 2100 lm (4ft. Glass)	16.5W 2100lm (U- Bent)⁵
		452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	463133, 463141, 463158	456566, 456574 456590, 456608 456616, 456624	452664, 452672, 452680, 452698
Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Osram Sylvania	QTP 1x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QTP 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QTP 3x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QTP 4x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 1x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 2x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 4x32T8/UNV ISN-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 1x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 2x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 3x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 4x32T8/UNV ISL-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 1x32T8/UNV ISH-SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 3x32T8/UNV ISH-SC	Not Recommended	Not Recommended	Not Recommended	Certified	Certified	Certified	
Osram Sylvania	QHE 4x32T8/UNV ISH	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 1x32T8/UNV ISH HT SC	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 2x32T8/UNV ISH HT SC	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 2x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4X32T8/UNV ISH-HT-1			Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 3x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 4x32T8/UNV ISN-SC-1	Certified	Certified	Certified	Certified	Not Recommended	Certified	
Osram Sylvania	QHE 2x32T8/UNV ISL-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC-1	Certified	Certified	Certified	Certified	Certified	Certified	
Ultrasave	UT232347	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Ultrasave	UT432347	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B132IUNVHP-N	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B232IUNVHP-N	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHP-A		Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B432IUNVHP-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B132IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B232IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	Certified
Universal Lighting Technologies	B332IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B432IUNVHE-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B132IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B232IUNVEL-A	Certified	Certified	Certified	Certified	Certified		Certified
Universal Lighting Technologies	B332IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B432IUNVEL-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B232IUNVHEH-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B332IUNVHEH-A	Certified	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B432I277HEH	Certified	Certified	Certified	Certified	Certified	Certified	

See footnotes on Page 8.

T8 programn		8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15 W 2100 lm (4ft.)	16.5W 2100lm (U- Bent) ⁵	
ballasts (fixed output) ¹		452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	452664, 452672, 452680, 452698	
Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	
Philips Advance	IOP-2PSP32-N				System Certified		
Philips Advance	IOP-3PSP32-SC	System Certified	System Certified	System Certified	System Certified		
Philips Advance	IOP-4PSP32-SC	System Certified	System Certified	System Certified	System Certified		
Philips Advance	IOP-2PSP32-LW-N				System Certified		
Philips Advance	IOP-3PSP32-LW-SC	System Certified	System Certified	System Certified	System Certified		
Philips Advance	IOP-4PSP32-LW-SC	System Certified	System Certified	System Certified	System Certified		
Philips Advance	HOP-2PSP32-HL-L				System Certified		
Philips Advance	HOP-4PSP32-HL-G				System Certified		
General Electric	GE-232MVPS-XL				Certified		
General Electric	GE-332MVPS-XL				Certified		
General Electric	GE-132MVPS-L						
General Electric	GE-232MVPS-L						
General Electric	GE-332MVPS-L						
General Electric	GE-432MVPS-L						
General Electric	GE-132MVPS-N				Certified		
General Electric	GE-232MVPS-N	Certified	Certified	Certified	Certified	Certified	
General Electric	GE-332MVPS-N	Certified	Certified	Certified	Certified		
General Electric	GE-432MVPS-N	Certified	Certified	Certified	Certified		
General Electric	GE-132MVPS-H				Certified		
General Electric	GE-232MVPS-H				Certified		
General Electric	GE-332MVPS-H				Certified		
General Electric	GE-432MVPS-H				Certified		
Osram Sylvania	QHE 1X32T8/UNV PSX-MC				Certified		
Osram Sylvania	QHE 1X32T8/UNV PSN-MC				Certified		
Osram Sylvania	QHE 2x32T8/UNV PSN-MC	Certified	Certified	Certified	Certified	Certified	
Osram Sylvania	QHE 3x32T8/UNV PSN-SC	Certified	Certified	Certified	Certified		
Osram Sylvania	QHE 4x32T8/UNV PSN-SC	Certified	Certified	Certified	Certified		
Osram Sylvania	QHES 2X32T8/UNV PSL-SC				Certified		
Osram Sylvania	QHE 2X32T8/UNV PSH-HT				Certified		
Osram Sylvania	QHE 3X32T8/UNV PSH-HT-SC				Certified		
Osram Sylvania	QHE 4X32T8/UNV PSH-HT				Certified		
Universal Lighting Technologies	B232PUNVHE-B	Certified	Certified	Certified	Certified	Certified	
Universal Lighting Technologies	B332PUNVHE-A	Certified	Certified	Certified	Certified		
	† ,	<u> </u>	T		T	1	

Certified

Certified

Certified

Certified

Certified

Universal Lighting Technologies

Universal Lighting Technologies

B432PUNVHE-A

B232PUNVHEH-A

T8 programmed-start ballasts (Dimmable)¹

15 W 2100 lm (4 ft.)

456897, 456905, 456913, 456921, 464248, 464255, 464263, 464271,

Manufacturer	Ballast Model	System Certified ³ / Certified ⁴	Dimmer Recommendation
Philips Advance	IZT-2S32-SC	System Certified	Use Compatible 0-10V dimmer
Philips Advance	IZT-4S32	System Certified	Use Compatible 0-10V dimmer
Philips Advance	REZ-132-SC	System Certified	Philips Lightolier - V1500EBUW Lutron - MRF2-6ND-120
Philips Advance	REZ-2S32-SC	System Certified	Philips Lightolier - V1500EBUW Lutron - MRF2-6ND-120
Philips Advance	REZ-3S32-SC	System Certified	Philips Lightolier - V1500EBUW Lutron - MRF2-6ND-120
General Electric	GE132MVPSN-V03	Certified	Use Compatible 0-10V dimmer
General Electric	GE232MVPSN-V03	Certified	Use Compatible 0-10V dimmer
General Electric	GE332MVPSN-VO3	Certified	Use Compatible 0-10V dimmer
General Electric	GE432MVPSN-VO3	Certified	Use Compatible 0-10V dimmer
General Electric	GE232MVPSH-V03	Certified	Use Compatible 0-10V dimmer
General Electric	GE332MVPSH-V03	Certified	Use Compatible 0-10V dimmer
General Electric	GE432MVPSH-V03	Certified	Use Compatible 0-10V dimmer

4-pin long compact instant-start ballasts¹

16.5 W 2100 lm (4-pin long compact 2 ft.)

456632, 456640, 456657

Manufacturer	Ballast Model	System Certified ³ / Certified ⁴
Philips Advance	ICN-1TTP40-SC	System Certified
Philips Advance	ICN-2TTP40-SC	System Certified
Philips Advance	ICN-3TTP40-SC	System Certified
General Electric	GE140MAX-A	Certified
General Electric	GE240MAX-A	Certified
General Electric	GE340MAX-A	Certified
Osram Sylvania	QHE1X40DL/UNV ISN-SC	Certified
Osram Sylvania	QHE2X40DL/UNV ISN-SC	Certified

T12 electronic ballasts¹

15 W 2100 lm (4 ft.)

456897, 456905, 456913, 456921, 464248, 464255, 464263, 464271,

Manufacturer	Ballast Model	System Certified ³ / Certified ⁴
Philips Advance	ICN-2S40-N	System Certified
Philips Advance	RELB-2S40-N	System Certified

Emergency ballasts ^{1,7}			8.5W 1050lm (2ft.)	10.5W 1200lm (3ft.)	12W 1600lm (4ft.)	15 W 2100 lm (4ft.)	17W 2100 lm (4ft. Glass)	16.5W 2100lm (U- Bent) ⁵	16.5 W 2100 lm (4-pin long compact 2 ft.)
			452011, 452029 452037, 452045	452052, 452060 452078, 452086	453589, 453597 453605, 453613, 464206, 464214, 464222, 464230	456897, 456905 456913, 456921, 464248, 464255, 464263, 464271,	456566, 456574 456590, 456608 456616, 456624	452664, 452672, 452680, 452698	456632, 456640 456657
Manufacturer	Emergency Ballast Model	# of lamps in Emergency	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Philips Bodine	(new) B50 (12NC: 913702456401)	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	LP600	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Bodine	LP600STU	1	Not Recommended	Not Recommended	System Certified	System Certified	System Certified	System Certified	System Certified
Philips Chloride	DEB-6LP	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham	FH7-UNV-500L	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham	FH11-UNV-750L-xx	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Fulham	FH12-UNV-1400L-xx	1	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	I-320	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	I-160 ⁶	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
lota Engineering	I-162	2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
Iota Engineering	ISL-54	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified
lota Engineering	nSI-5408	1 or 2	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified	System Certified

CFL ballasts^{1,2} 10.5W. 900 lm 85W. 900 lm (Vertical Configuration) (Horizontal Configuration) 458406, 458414, 458364, 458372, 458422, 458430 458380, 458398 System Certified3/ Manufacturer **Driver Model** System Certified3/Certified4 Certified⁴ Philips Advance ICF-2S13-M1-BS System Certified System Certified Philips Advance ICF-2S13-H1-LD System Certified System Certified System Certified Philips Advance ICF-2S13-M1-BS-QS System Certified Philips Advance ICF-2S26-H1-LD System Certified System Certified8 Philips Advance ICF-2S26-M1-BS System Certified System Certified Philips Advance ICF-2S26-M1-BS-QS System Certified System Certified Philips Advance ICF-2S18-H1-LD System Certified System Certified Philips Advance ICF-2S18-M1-BS System Certified System Certified Philips Advance ICF-2S18-M1-BS-QS System Certified System Certified System Certified Philips Advance ICF-2S42-M2-LD System Certified Philips Advance ICF-2S42-M2-BS System Certified System Certified Philips Advance ICF-2S42-90C-M2-BS System Certified System Certified Philips Advance ICF-2S42-90C-M2-LD System Certified System Certified General Electric Certified GEC218-MVPS-SE Certified Universal Lighting Technologies C218UNVME Certified Certified Universal Lighting Technologies C2642UNVME Certified Certified Certified Osram Sylvania QTP 1/2X18CF/UNV DM Certified

QTP 2X26CF/UNV DM

EP2/26CF/MV/2

Systems on this page are:

Osram Sylvania

Howard Industries



See footnotes on Page 8.

Emergency ballasts
(for compact
fluorescent lamps) ^{1,7}

	450264 450272
458406, 458414,	458364, 458372,
458422, 458430	458380, 458398

Horizontal Lamp

Vertical Lamp

Manufacturer	Emergency Ballast Model	# of lamps in Emergency	System Certified ³ / Certified ⁴	System Certified ³ / Certified ⁴
Philips Bodine	(new) B50 (12NC:913702456401)	1	System Certified	System Certified
Philips Bodine	(new) B30 (12NC:913702461001)	1	System Certified	System Certified
lota	I-42	2		System Certified
lota	I-420	1 or 2	System Certified	System Certified
lota	I-160	1	System Certified	
lota	I-160	2	System Certified	System Certified
Fulham	FH11-UNV-750L (2)	2	System Certified	System Certified
Fulham	FH12-UNV-1400L (2)	2	System Certified	System Certified

T12 Rapid-Start Magnetic Ballasts^{1,2}

Certified

Certified

Certified

Certified

463117, 463125

Manufacturer	Ballast Model	System Certified ³ / Certified ⁴
Philips Advance	R-140-1-TP	System Certified
Philips Advance	RL-140-TP	System Certified
Philips Advance	X-140-TP	System Certified
Philips Advance	R-2S40-1-TP	System Certified
Philips Advance	XQM-2S40-TP	System Certified
Philips Advance	V-2S40-1-TP	System Certified
Philips Advance	RQM-2S40-3-TP	System Certified
Philips Advance	R-2S34-TP-5	System Certified
Philips Advance	V-2S34-TP	System Certified
Philips Advance	RM-2S35-TP	System Certified
General Electric	GEM240RS277	Certified
General Electric	GEM240RS120 -1	Certified
Howard Industries	M1/40RS-120	Certified
Howard Industries	M2/40RS-277	Certified
Howard Industries	M2/40RS-240 -1	Certified
Universal Lighting Technologies	412-L-SLH-TC-P	Certified
Universal Lighting Technologies	458-L-SLH-TC-P	Certified
Universal Lighting Technologies	540-L-TC-P	Certified
Universal Lighting Technologies	NO.446-L-LH-TC-P-7	Certified
Universal Lighting Technologies	443-L-SLH-TC-P	Certified
Universal Lighting Technologies	446-L-SLH-TC-P	Certified
Osram Sylvania	MB1x40/277 RS-1	Certified
Osram Sylvania	MB1x40/120RS-1	Certified
Osram Sylvania	MB2x40/120RS-1	Certified
Osram Sylvania	MB2x40/277RS-1	Certified
Industrias Sola Basics S A DE C V	E420-F-234 IC -1	Certified
Radionic Industries Inc.	NO.ES240HTP	Certified

- 1. Ballast tests are performed with a specific date code. Please contact the factory for date code information.
- 2. UL/CSA Classified with the listed ballasts / drivers
- 3. System performance (Philips InstantFit LED T8 lamp and ballast) has been evaluated by the lamp and ballast manufacturer.
- 4. System performance (Philips InstantFit LED T8 lamp and ballast) has been evaluated by the lamp manufacturer only.
- 5. Typical application for U-Bent Lamps is with 2-lamp ballasts.
- 6. Connect BRN/BRN-W leads.
- 7. Please contact the emergency ballast manufacturer for wiring diagrams.
- 8. 2 lamp operation only.
- * Please contact Philips for questions about third party ballasts that are not on this list. Information in this document is subject to change without prior notice.











© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLt-16118CR 05/16



Philips Lighting North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Tel. 855-486-2216

Imported by: Philips Lighting, A division of Philips Electronics Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008