

PHILIPS

Linear fluorescent
tube

TL-D Super 80

58 W

G13

Cool daylight

927983286536



Vibrant experience with extra brightness

Philips Color 80s offer higher light output for extra brightness and better ambiance. They are suitable for applications where light quality is important for a more vibrant experience.

Saves energy

- Saves energy

Gives you bright light

- Vibrant experience with extra brightness

Highlights

Saves energy Bright boost

High efficient fluorescent combined with BrightBoost technology for good color rendering and extra brightness

Specifications

Bulb characteristics

- Dimmable: No
- Socket: GU10

Durability

- Nominal lifetime: 15,000 hour(s)

Light characteristics

- Color rendering index (CRI): 80
- Light Color Category: Cool Daylight

Power consumption

- Wattage: 58 W

Technical specifications

- Light output: 4,800 lumen
- Shape: Linear fluorescent tube

Packaging dimensions and weight

- EAN/UPC - product: 8711500284969
- Net weight: 0.230 kg
- Gross weight: 0.260 kg
- Height: 2.700 cm
- Length: 150.000 cm
- Width: 2.700 cm
- Material number (12NC): 927983286536



Issue date: 2022-10-22
Version: 0.490

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com