



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

Example: 1010 H

Product Code	Finish
1010	
1010 Landscape Beacon	H Bronze

Specifications

Housing

Die-cast aluminum. Removable roof for easy relamping. Fasteners are 300 series stainless steel. Molded silicone gasket seals glass, top and bottom, and prevents moisture intrusion into the fixture. NOTE: The base has two (2) ½" NPT conduit entrances for connection to the power source.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

Optical Assembly

Clear borosilicate glass refractor lens. Fully gasketed top and bottom.

Lamping

10W maximum A19 lamp.

Electrical Assembly

Incandescent is medium base porcelain socket with nickel-plated screw shell and center contact.

Installation & Mounting

VOLTAGE CAUTION: Some local interpretation of the NEC Section 210-6 only permit the use of 120 volt fixtures when they are mounted below 8'. Check with local authorities before specifying alternate voltages. Beacons are partially recessed. Potting compound must be used to seal the conduit wire entry. Lower housing may be recessed directly in the ground or in concrete

Warranty

Three-year limited warranty.

Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 standards.

Height	Width	Max. Weight
9 1/32" (229mm)	8 3/8" (213mm)	6.30 lb

