




4

PSED version (Emergency Lighting)

	AC Lumen output	AC power [W]	DC Lumen output	DC power [W]
BY470P 130S	13000	106	2000	16
BY471P 170S	17000	134	2600	21
BY471P 250S	25000	200	3800	31

For emergency lighting is required DC power connection (220-240V DC)

Philips GentleSpace

Mounting instructions

- Instructions de montage
Montageanleitung
Montage instructie
Instruzioni di montaggio
- Instrucciones de montaje
Instruções de montagem
Monteringsinstruktioner
Monteringsvejledning
- Kokoonpano- ja kiinnitysohjeet
Montaj yönergəsi
Οδηγίες συναμολογήσης
Instrukcja montazu
- Szerelési utasítások
Návod k montáži
Инструкция по монтажу
Návod k montáži


LEDs

~220 V...240V
50 Hz/60 Hz

Inrush current
108A / 140µs

IP65

	LEDs	W	kg	IK 07	max	min			Maximum number of luminaire on MCB 16A	GreenWarehouse
BY470P 130S	176	106	9,3	●	45°C	-30°C	25cm	●	10	
BY471P 170S	264	134	15,2	●	45°C	-30°C	25cm	●	10	
BY471P 250S	352	200	15,6	●	45°C	-30°C	25cm	●	5	
BY470X 130S	176	108	9,8	●	45°C	-30°C	25cm	●	10	●
BY471X 170S	264	136	15,7	●	45°C	-30°C	25cm	●	10	●
BY471X 250S	352	205	16,1	●	45°C	-30°C	25cm	●	5	●
BY470P 130S BR	176	106	11,1	●	45°C	-30°C	25cm	●	10	
BY471P 170S BR	264	134	17,0	●	45°C	-30°C	25cm	●	10	
BY471P 250S BR	352	200	17,4	●	45°C	-30°C	25cm	●	5	
BY470X 130S BR	176	108	11,6	●	45°C	-30°C	25cm	●	10	●
BY471X 170S BR	264	136	17,5	●	45°C	-30°C	25cm	●	10	●
BY471X 250S BR	352	205	17,9	●	45°C	-30°C	25cm	●	5	●



Disconnect before servicing
Mettre hors tension avant intervention
Öffnen nur spannungsfrei

Demonderen voor onderhoud
Togliere tensione prima di fare manutenzione
Desconectar antes de manipular

Bryt strömmen före lampbyte

