



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: B4 A LED18 NF W S

Product Code	B4	LED Aluminum Bullyte
<b>Finish</b>	A H G	Black Bronze Verde
<b>Source/Lumens</b>	LED18	18W LED
<b>Optics</b>	NF	Narrow Flood
<b>CCT</b>	W	Warm
<b>Shroud</b>	S L	Short Shroud Long Shroud

\*1 Lamp will be shipped with fixture, but not installed. Lamp not sold separately.

### Specifications

#### HOUSING:

Fully rotatable shroud, gasketed, cast aluminum. Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. Shroud is optional. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

#### FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

#### OPTICAL ASSEMBLY:

Clear Tempered flat glass lens (glass comes with shroud)

#### LAMPING:

18W lamp with 25° beam spread, 25,000 hours life. Color temperature (CCT): warm white (3,000K nominal). No Mercury.

#### CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

#### WARRANTY:

Three-year limited warranty.

#### Width:

6 1/4" (159mm)

#### Length:

8-9/16" 218mm, (S)10-3/16" 259mm,(L)16-1/2" 419mm

#### Max. Weight:

2.2 lb., (S) 4.5 lb., (L) 8.15 lb.

