




PHILIPS

TrueLine

RC 530B



		Sensor/ Blind sensor holder .		kg VPC	kg PCV	kg BCV
Recessed	VPC	A	B			
		W8L120	1197	1130	2.6	
				1170	2.8	
		W8L125	1247	1130	2.8	
Recessed	PCV			1170	2.9	
		W8L150	1497	1410	3.2	
				1450	3.3	
		W8L113	1152	1130		2.6
Recessed	PCV	W8L117	1192	1170		2.8
		W8L141	1432	1410		3.1
		W8L145	1472	1450		3.4
		W8L113	1127		2.5	2.7
Recessed Line	VPC/PCV	W8L117	1167		2.7	2.9
		W8L141	1408		3.0	3.2
		W8L145	1448		3.2	3.5
Recessed	BCV	W15L172	1722			4.1



Optional:


RC530Z
EP SET WH



4x(M3)



2x(M4)



2x





Recessed
(add safety cable if required)




2x

1





Wieland







2

3





PC V
















4

5







Recessed Line








Push-in (PIP) PSD
PI-5
Line End / Line Feature





8a

PI-7
Line End / Line Feature




8b




9




asymmetric
LightEngine




10a




10b



10c




10d




PoE

Condition Philips to specify to the customers (instruction):
> to use UTP (Unshielded Twisted Pair) CAT5E or CAT6 cable.
> the maximum length of the cable to be 20 meters.
Apply a minimum radius of the Ethernet cable of 4x the cable diameter.






Cover remove (ZZS400 OCR)




Replace 10a, b, c



ACL/MDU versions only



Inrush current



PSD

I _{max} .(A)	21
T _{ref} (μs)	280
Condition: Input voltage 230V	
MCB	Luminaires Max.
B-16A	24

SRD

I _{max} .(A)	21
T _{ref} (μs)	280
Condition: Input voltage 230V	
MCB	Luminaires Max.
B-16A	21