


## Landscape

## Composite Inground

i35 INC Inground






## **Ordering Guide**

Example: I35 N

Product Code	135	Incandescent
Finish	N	Natural Bronze



## **Specifications**

### HOUSING

Potted factory seal with anti-wicking wiring between grade-level junction compartment and ballast compartment. Isolated ballast compartment with slotted, silicone-gasket cover. Single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. Separate sealed compartments provide isolation between field wiring, optics, and ballast. Isolated, grade-mounted sealed wiring compartment with two (2) 3/4" threaded conduit inlets in bottom for feed-through wiring capabilities and supplied with gel-filled wire nuts. Cast cover to match trim ring with two captive stainless steel slotted Phillips machine screws for access. Trim ring is natural cast bronze. Rock guard used for directional glare control made of natural cast bronze. Ring is factory pre-drilled for optional guard. Lens ring is hinged with two captive stainless slotted Phillips machine screws for access to lamping compartment (tamper-resistant screws available upon request.)

### FINISH:

Natural bronze has satin matte finish. Composite is pressure formed, molded-in color.

### LAMPING:

Lamp is not included. 150W maximum PAR38/R40 incandescent lamp.

## OPTICAL ASSEMBLY:

Clear, slightly convexed, molded borosilicate glass, high impact, 3000 lb. live load rated, drive-over glass, with molded wrap around 100% silicone lens gasket. Aiming 15° either side of vertical and full 360° rotation. Angle degree marks for precise vertical aiming with tool-less aiming. Handle enables easy tool-less removal of optical assembly for hot aiming and re-lamping, simply press-fit back into place.

# i35 Composite Inground

## **INC Inground**

### **Specifications**

## **ELECTRICAL ASSEMBLY:**

Slotted ballast assembly with Quick Disconnects mounted to cast aluminum bracket for easy maintenance.

#### CERTIFICATIONS

Manufactured to ISO 9001:2008 Standards. ADA compliant when used in concrete and flush mounted with CPS25. ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations.

### WARRANTY:

Ten-year limited warranty.

#### IP RATING:

IP66/68: Dust-tight and dual rated - sealed against direct jets of water and against continuous submersion in water tested to 1 meter (3.28 feet).

### Height:

15 3/4

### Width:

7 1/2

### Depth:

9 3/4

